

EdgeConnect™ Single Receptacle,
Tamper Resistant, 15A, 125V,
Orange

By Hubbell Wiring Device-Kellems
Catalog # [HBL8210STOTR](#)

EdgeConnect™ Single Straight Blade Receptacle, Screwless Termination Technology, Hospital Grade, Tamper Resistant, 15A Orange

Features

- Color coded plungers for simpler installation
- Accepts 14-10 AWG solid or stranded wire for any application
- Reduce your installation time and move on to your next job faster
- Easily rewire by using built in leverage points to life plungers with small screwdriver

Application

Spring clamp terminal strengthens over time providing a more reliable connection.

General

Catalog Number	HBL8210STOTR
Color	Orange
Series	EdgeConnect™
Style	Tamper Resistant
Type	Single Receptacle
UPC	783585966878

Electrical Ratings

Amperage Rating	15 A
Voltage Rating	125 V



Conductor Related

Wire Size	14-10AWG Solid or Stranded
-----------	----------------------------

Certifications And Compliance

Industry Standard(s)	UL Listed to UL498 File No. E2186, Certified to CSA 22.2, No. 42 File 285, NEMA® WD-6 Compliant
Nema Rating	NEMA® WD-6 Compliant

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Installation Manuals - HUBBELL EDGEConnect™ SCREWLESS TERMINATION SINGLE RECEPTACLES](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M-14631](#)
- [Specifications - HBL8210STOTR](#)
- [Video - Hubbell® EdgeConnect™ Technology](#)