



# Hospital Grade Surge Suppression Receptacle, Duplex, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Almond

By Hubbell Wiring Device-Kellems  
 Catalog # [HBL8362ALSA](#)



Hospital Grade Surge Suppression Receptacle, Duplex, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Almond

## Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol for visual identification of surge suppression receptacle

## Application

Decorator Duplex with Light and Alarm

## General

Color	Almond
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> <li>• Electrical - Frequency - 60Hz</li> <li>• Electrical - Protection Modes - Normal and Common Modes</li> <li>• Electrical - Response Time - Approximately 5 ns</li> <li>• Electrical - Transient Suppression - Peak Energy (10 X 100 <math>\mu</math>s) Peak Current (8 X 20 <math>\mu</math>s)</li> <li>• Electrical - Voltage - 120V AC + 10% - 15%</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)</li> </ul>

Response Time 5

## Dimensions

Display Size Standard

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Certifications and Compliance

- |                      |   |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> <li>• CSA Certified to Specification C22.2 No. 42</li> <li>• Listed to UL Standards 498 Receptacles</li> <li>• UL Listed File E2186</li> </ul> |
|----------------------|---|

Nema Rating 5-20R

## Logistics

Carton Quantity 10

## Product Assets

- [Engineering Drawing - HBL8362ALSA AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1152\\_INSTALLINST](#)
- [Literature - WLBD026\\_Duct Products Brochure\\_WEB](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK\\_HBL8362\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Series  
Type  
UPC

Hospital Grade  
Duplex  
783585436111



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HBL8362ALSA-SPEC-EN | REV 5/2023