



Surge Protective Devices, SPIKESHIELD Hospital Grade Surge Suppression Receptacle, Duplex, 20A 125V, 5-20R, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL8362GYSA](#)



Surge Protective Devices, SPIKESHIELD Hospital Grade Surge Suppression Receptacle, Duplex, 20A 125V, 5-20R, Gray

Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol for visual identification of surge suppression receptacle

Application

Decorator Duplex with Light and Alarm

General

Color	Gray
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Performance	<ul style="list-style-type: none"> • Electrical - Frequency - 60Hz • Electrical - Protection Modes - Normal and Common Modes • Electrical - Response Time - Approximately 5 ns • Electrical - Transient Suppression - Peak Energy (10 X 100 μs) Peak Current (8 X 20 μs) • Electrical - Voltage - 120V AC + 10% - 15% • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications and Compliance

- | | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • CSA Certified to Specification C22.2 No. 42 • Listed to UL Standards 498 Receptacles • UL Listed File E2186 |
|----------------------|---|

Nema Rating 5-20R

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - Wiring M16 Catalog page](#)
- [Catalog Page - Wiring N-13 Catalog page](#)
- [Catalog Page - Wiring J-4 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - HBL8362GYSA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1152_INSTALLINST](#)
- [Literature - WLBD026_Duct Products Brochure_WEB](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - SpikeShield® Power Quality Surge Protective Devices](#)
- [Sales Drawings - WDK_HBL8362_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Series
Type
UPC

Hospital Grade
Duplex
783585060453



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBL8362GYSA-SPEC-EN | REV 5/2023