

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 8-Outlet with Telephone/Satellite, 2100 Joules, 6' Cord, Office White

By Hubbell Wiring Device-Kellems
Catalog # [HBL8PS2100DA](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A
125V, 8-Outlet with Telephone/Satellite, 2100 Joules, 6' Cord,
Office White

Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.

General

EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	Electrical - Max Surge Current - 39.0kA
	Electrical - Max. Operating Voltage - 130
	Electrical - Operating Frequency - 50/60Hz
	Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
Response Time	5
UPC	783585120591

Dimensions

Display Size	2100 Joules
--------------	-------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 VAC

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL8PS2100DA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2380_INSTALLINST](#)
[Sales Drawings - WDK_HBL8PS2100DA_DRAWING_PDF](#)
[Warranty - Surge Plug Strips](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-HBL8PS2100DA-SPEC-EN | REV 6/2024