

Temporary Lighting Products, LED
Cord Reel with Flashlight End, 40',
18/2 SJTOW Cord

By Hubbell Wiring Device-Kellems
Catalog # [HBLC40182LED](#)

Temporary Lighting Products, LED CordReel with Flashlight End,
40', 18/2 SJTOW Cord

Features

- Covered on/off switch located on handle to control side and end LEDs
- Flash light or floor light capable with end light feature
- Desired cord length automatically maintained through positive latch mechanism
- Constructed of durable corrosion-resistant steel

General

Cable Length	40 Ft
Cable Type	#18/2 SJTOW
Catalog Number	HBLC40182LED
EU RoHS Indicator	Contact Manufacturer
Series	Commercial
Style	LED
Type	Reel With Hand Lamp
UPC	783585467399

Electrical Ratings

Amperage Rating	0.65 A
-----------------	--------



Current / Amperage Rating	0.65 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Logistics

Carton Quantity	4
Pallet Quantity	96

Product Assets

- [Catalog Page - WDK J-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_HBLC40182LED_INSTALLINST](#)
- [Literature - Cord Reels](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Safety Product Guide](#)
- [Literature - Temporary Industrial Lighting](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_HBLC40182LED_DRAWING_PDF](#)
- [Specifications - HBLC40182LED](#)
- [Warranty - Industrial & Commercial Products](#)