



Straight Blade Devices, Colored Cord Clamps, Insulgrip Size 1, Orange

By Hubbell Wiring Device-Kellems
Catalog # [HBLCORDCLAMPOR](#)



Straight Blade Devices, Colored Cord Clamps, Insulgrip Size 1, Orange

Features

- Cord Mounted

General

| | |
|------------------------------|-------------------------------|
| Color | Orange |
| Cord Range | 0.230"-0.720" (5.8-18.3) |
| Item Type | Insulgrip Plug |
| Material - Mounting Hardware | Cord Mounted |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Series | Accessory |
| Style | Colored Cord Clamp |
| UPC | 783585541068 |

Dimensions

| | |
|--------|--------|
| Weight | 0.1 lb |
|--------|--------|

Electrical Ratings

| | |
|-----------------|--------------|
| Amperage Rating | 20 A |
| Current Rating | 20 A |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - Wiring A-34 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Literature - Entertainment Product Solution Guide](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[HBL5669C - Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 15A 250V, 6-15R and White](#)
[HBL5469C - Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 20A 250V, 6-20R and White](#)
[HBL5366C - Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 20A 125V, 5-20P and White](#)
[HBL5666C - Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 250V, 6-15P and White](#)
[HBLCORDCLAMPY - Straight Blade Devices, Colored Cord Clamps, Insulgrip Size 1, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBLCORDCLAMPOR-SPEC-EN | REV 5/2023