

Industrial Grade, MotorQuick Disconnect, Unfused Switch, 3 Pole, 30A 600V AC,IP69k, NEMA Type 4X, 12 Non-Metallic Sloped Top Enclosure, 5' Pre-Wired Female Cable

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS30MQ5](#)



Industrial Grade, MotorQuick Disconnect, Unfused Switch, 3 Pole, 30A 600V AC,IP69k, NEMA Type 4X, 12 Non-Metallic Sloped Top Enclosure, 5' Pre-Wired Female Cable, cULus, NSF, CE, UL 508 / UL 60947-4-1A

Application

Heavy Duty Industrial and/or Washdown

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage
- Electrical - Dielectric Voltage - Withstands 3000V AC minimum
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V0 Classification
- Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

Catalog Number	HBLDS30MQ5
Color	Gray
Enclosure Type	IP69k and UL Type 4X, 12
Environmental Conditions	Indoor and Outdoor
Horsepower - Maximum	15
Ingress Protection	IP69k, NEMA Type 4X, 12
Material - Mounting Hardware	Stainless Steel Screw Mounting
Mounting Method	External fully adjustable feet
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum

Series Specifications	-40 °C
	Non-Fused
Style Type UPC	• Base - Valox®
	• Enclosure Gasket - Neoprene
	• Handle - Valox®
	• Shaft (Unfused) - Valox®
	• Top - Valox®
	Heavy Duty Disconnect Switches 783585763217

Dimensions

Height	4.12 in
Hub Size	3/4"
Weight	4.9 lb

Electrical Ratings

Current / Amperage Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute

Conductor Related

Wire Size	#14 AWG to #8AWG
-----------	------------------

Certifications And Compliance

Industry Standard(s)	cULus Listed
----------------------	--------------

Product Assets

[Brochures - Circuit-Lock® Motor Disconnects](#)
[Catalog Page - WDK F-13 Catalog Page](#)
[Installation Manuals - HUBBELL 30 AMP CIRCUIT-LOCK DISCONNECT SWITCH | Installation manual](#)

Literature - Circuit-Lock® Rounded Sloped Top Motor
Disconnects
Specifications - HBLDS30MQ5

Warranty - Industrial & Commercial Products
Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBLDS30MQ5-SPEC-EN | REV 7/2025