

Industrial Grade, MotorQuick
Disconnect, Unfused, 3 Pole, 30A
600V AC,IP69k, NEMA Type 4X,12
Non-Metallic Sloped Top
Enclosure,1 Pre-Wired LINKOSITY
Receptacle

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS30MQR](#)



Industrial Grade, MotorQuick Disconnect, Unfused, 3 Pole, 30A
600V AC,IP69k, NEMA Type 4X,12 Non-Metallic Sloped Top
Enclosure,1 Pre-Wired LINKOSITY Receptacle, cULus, NSF, CE,
UL 508 / UL 60947-4-1A

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Significantly reduces downtime to replace a motor with plug-and-play LINKOSITY® technology.

Application

Heavy Duty Industrial and/or Washdown

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage
- Electrical - Dielectric Voltage - Withstands 3000V AC minimum
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V0 Classification
- Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact
- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C

- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

General

Catalog Number	HBLDS30MQR
Color	Gray
Enclosure Type	IP69k and UL Type 4X, 12
Environmental Conditions	Indoor and Outdoor
Horsepower - Maximum	15
Ingress Protection	IP69k, NEMA Type 4X, 12
Material - Mounting Hardware	Stainless Steel Screw Mounting
Mounting Method	External fully adjustable feet
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C
Series	Non-Fused
Specifications	• Base - Valox® • Enclosure Gasket - Neoprene • Handle - Valox® • Shaft (Unfused) - Valox® • Top - Valox®
Style	Heavy Duty
Type	Disconnect Switches
UPC	783585763187

Dimensions

Height	4.12 in
Hub Size	3/4"
Weight	2.95 lb

Electrical Ratings

Current / Amperage Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute

Conductor Related

Wire Size	#14 AWG to #8AWG
-----------	------------------

Certifications And Compliance

Industry Standard(s)	cULus Listed
----------------------	--------------

Product Assets

- [Brochures - Circuit-Lock® Motor Disconnects](#)
- [Catalog Page - WDK F-13 Catalog Page](#)
- [Installation Manuals - HUBBELL 30 AMP CIRCUIT-LOCK DISCONNECT SWITCH | Installation manual](#)
- [Literature - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)
- [Specifications - HBLDS30MQR](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)

