



# Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA 4X Enclosure, with Aux Contact AC2

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS3AC2](#)



Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA 4X Enclosure, with Aux Contact AC2

## Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Reversible interior accomodates top or bottom conduit opening

## Application

Labelless

## General

Enclosure Type	Type 4X, IP69k
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current &amp; voltage</li> <li>• Electrical - Dielectric Voltage - Withstands 3000V AC minimum</li> <li>• Electrical - Max. Working Voltage - 600V AC RMS</li> <li>• Environmental - Flammability - UL94-5VA and V0 Classification</li> <li>• Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact</li> <li>• Environmental - UV Resistance - All materials are UV stabilized</li> <li>• Mechanical - Impact Resistance - In accordance</li> </ul>
-------------	--

## Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Width	6 in

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

## Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Product Assets

[Installation Manuals - WIRING\\_PD1782\\_PD1789\\_INSTALLINST Literature - WIRING\\_WLFVM034 Literature - Improved Short Circuit Current Ratings \(SCCR\) Literature - Pulp & Paper Solutions Warranty - Industrial & Commercial Products](#)

## Related Products

[HBLDS3RC - Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Replacement Cover for 30A](#)  
[HBLDS6AC - Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 60A 600V AC, Screw Terminals, NEMA 4X Enclosure, With Aux Contact](#)  
[HBLDS3VFD - Industrial Grade, Variable Frequency Drive, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, NEMA](#)  
[HBLDS3ACNK - Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, NEMA4X Enclosure, With Aux Contact](#)  
[HBL30RGB - Switches and Lighting Controls, Mechanical Interlock, Replacement Parts, Replacement Ground Block, For 30A.](#)

Resistance in accordance with UL 746C

- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Series

Non-Fused

Style

Heavy Duty

Type

Disconnect Switches

UPC

783585145440



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HBLDS3AC2-SPEC-EN | REV 5/2023