



Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With 1) Pre-Wired LINKOSITY Female Receptacle

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3SSRMQR](#)



Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With 1) Pre-Wired LINKOSITY Female Receptacle

General

EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Type 4X
Horsepower - Maximum	15
Ingress Protection	IP67
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance

- Electrical - Dielectric Voltage - 2,200V AC minimum for 1 minute
- Electrical - Electrical Life - 6,000 cycles with load
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and VO Classification
- Environmental - Operating Temperature - Max. continuous 75°C, Min. continuous -40°C
- Mechanical - Impact Resistance - UL746C
- Mechanical - Mechanical Life - 10,000 minimum cycles
- Mechanical - Terminal Accommodations - 30A, #14 AWG Min. - #10 AWG Max
- Mechanical - Terminal Torque - 30A, 20 inch pounds

Series	MotorQuick/LINKOSITY
Type	Disconnect Switches
UPC	783585541587

Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pre-Wired
Current Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute
Phase	Three Phase

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Listed to UL 2238 and UL 50E • UL 508, Industrial Control Equipment File #E36355
----------------------	---

Product Assets

- [Catalog Page - Wiring F-17 Catalog page](#)
- [Catalog Page - Wiring F-11 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Labelless Disconnects](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Safety Product Guide](#)
- [Literature - Food Processing Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - M12748](#)
- [Warranty - Industrial & Commercial Products](#)

Related Products

- [HBLDS3SSMQ5 - Disconnect Switches, Square top Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With 5' Pre-Wired Female Cable](#)
- [HBLDS3MQR - Industrial Grade, MotorQuick Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, With 1\) Pre-Wired LINKOSITY Female Receptacle](#)
- [RF3004PA001 - Signal and Control Products, Linkosity, Receptacle 30A 4W, 1'](#)
- [HBLDS3SSRMQR2 - Disconnect Switches, Sloped Enclosure, 30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With 2\)](#)

Length
Width

8.5 in
6 in

Pre-Wired LINKOSITY Receptacles
HBLDS3SSMQR2 - Disconnect Switches, Square top Enclosure,
30A 600V AC, Non-Fused, NEMA 4X, Stainless Steel, With 2)
Pre-Wired LINKOSITY Receptacles



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HBLDS3SSRMQR-SPEC-EN | REV 5/2023