

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic Sloped Version
Replacement Cover for 60A With inTOUCH Installation Free LED Phase Indication and Jog - HBLDS60 and HBLDS60T Series

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS60RCPJ](#)

Industrial Grade, Motor Disconnect, Unfused Switch, Non-Metallic
Replacement Cover for 60A With inTOUCH Installation Free LED Phase
Indication and Jog, HBLDS60 and HBLDS60T Series

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Certified by NSF for hygiene in food processing applications
- Product rating are permanently laser-marked and will not wash off
- Six highly visible integral phase identification LEDs for use on 3 Phase Y or Delta systems provide secondary means of visual confirmation of make/break on all phases

Application

Heavy Duty Industrial and/or Washdown

Specifications

Industry Standard(s)	cULus Listed
Environmental Conditions	Indoor and Outdoor

Dimensions

Weight	1.85 lb.
--------	----------

General

Specifications	Enclosure Gasket - Neoprene
----------------	---



	- Handle - Valox® - Shaft (Unfused) - Valox® - Top - Valox®
Color	Gray
Style	Replacement Cover
Ingress Protection	IP69k, NEMA Type 4X, 12
Product Family	Non-Fused
UPC	783585763323
Type	Accessories
Material - Mounting Hardware	Stainless Steel Screw Mounting
Enclosure Type	IP69k and UL Type 4X, 12

Logistics

Pallet Quantity	1
Carton Quantity	1

Operational

Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Without Impact Maximum continuous 75°C and minimum -40 °C

Product Assets

- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)
- [Sales Drawing \[English\]](#)