

Motorized Cord Reel, 25ft, #12/3
SJO, Black Portable Outlet Box with
GFCI Module and (2) 20A Tamper
Resistant Duplex Receptacles

By Hubbell Wiring Device-Kellems
Catalog # [HBLM25123GF220M1](#)

Motorized Cord Reel, 25ft, #12/3 SJO, Black Portable Outlet Box
with GFCI Module and (2) 20A Tamper Resistant Duplex
Receptacles

Features

- Durable, Corrosion Resistant Cast Aluminum Housing and Base
- UL Type 17
- Multi-Position Guide Arm can be mounted in two different positions
- Ratchet lock automatically maintains desired cord length or can be disengaged in the field for constant tension applications

General

Cable Length	25 (7.62)
Cable Type	12/3 SJO
Catalog Number	HBLM25123GF220M1
Color	White
Series	Motorized
Style	Industrial



UPC 783585974545

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	250

Certifications And Compliance

Industry Standard(s)	UL 355 Listed
----------------------	---------------

Product Assets

- [Brochures - inREACH® Motorized Cord Reels](#)
- [Installation Manuals - Hubbell Motorized Electric Cord Reels](#)
- [Literature - inREACH™ Motorized Cord Reels - FAQ](#)
- [Specifications - HBLM25123GF220M1](#)
- [Video - inREACH motorized cord reel](#)
- [Video - inREACH Motorized Cord Reel](#)