

# Motorized Cord Reel, 25ft, #12/4 SJO, Wire Leads

By Hubbell Wiring Device-Kellems  
Catalog # [HBLM25124C](#)

Motorized Cord Reel, 25ft, #12/4 SJO, Wire Leads



\*Representative Image

## Features

- Durable, Corrosion Resistant Cast Aluminum Housing and Base
- Multi-Position Guide Arm can be mounted in two different positions
- Ratchet lock automatically maintains desired cord length or can be disengaged in the field for constant tension applications

## General

Catalog Number	HBLM25124C
Color	Black
Series	Motorized
Style	Industrial Power
UPC	783585789187

## Dimensions

Cable Length Active	25
---------------------	----

## Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125/250 V

## Conductor Related

Cord Type	Black
-----------	-------

## Certifications And Compliance

Industry Standard(s)	UL 355 Listed
----------------------	---------------

## Product Assets

- [Brochures - inREACH® Motorized Cord Reels](#)
- [Installation Manuals - Hubbell Motorized Electric Cord Reels](#)
- [Literature - inREACH™ Motorized Cord Reels - FAQ](#)
- [Specifications - HBLM25124C](#)
- [Video - inREACH motorized cord reel](#)
- [Video - inREACH Motorized Cord Reel](#)