

Motorized Cord Reel, Black, 25ft,
#12/3 SJO,

By Hubbell Wiring Device-Kellems
Catalog # [HBLM45123BLKR220M1](#)

Motorized Cord Reel, Black, 25ft, #12/3 SJO,

Features

- Durable, Corrosion Resistant Cast Aluminum Housing and Base
- UL Type 27
- Multi-Position Guide Arm can be mounted in two different positions
- Ratchet lock automatically maintains desired cord length or can be disengaged in the field for constant tension applications

General

Cable Length	45 (13.72)
Cable Type	12/3 SJO
Catalog Number	HBLM45123BLKR220M1
Color	White
Series	Motorized



Style	Industrial
UPC	783585974620

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	250

Certifications And Compliance

Industry Standard(s)	UL 355 Listed
----------------------	---------------

Product Assets

[Brochures - INREACH® Motorized Cord Reels](#)
[Literature - inREACH™ Motorized Cord Reels - FAQ](#)
[Specifications - HBLM45123BLKR220M1](#)
[Video - inREACH motorized cord reel](#)
[Video - inREACH Motorized Cord Reel](#)