

Motorized Cord Reel, 45ft, #12/4  
SJO, Split Circuit

By Hubbell Wiring Device-Kellems  
Catalog # [HBLM45124SC](#)

Motorized Cord Reel, 45ft, #12/4 SJO, Split Circuit



\*Representative Image

Features

- Durable, Corrosion Resistant Cast Aluminum Housing and Base
- Multi-Position Guide Arm can be mounted in two different positions
- Ratchet lock automatically maintains desired cord length or can be disengaged in the field for constant tension applications

General

Catalog Number	HBLM45124SC
Color	Black
Series	Motorized
Style	Industrial Power
UPC	783585789248

Dimensions

Cable Length Active	45
---------------------	----

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125/250 V

Conductor Related

Cord Type	Black
-----------	-------

Certifications And Compliance

Industry Standard(s)	UL 355 Listed
----------------------	---------------

Product Assets

- [Literature - inREACH™ Motorized Cord Reels - FAQ](#)
- [Specifications - HBLM45124SC](#)
- [Video - inREACH motorized cord reel](#)
- [Video - inREACH Motorized Cord Reel](#)