

Heavy Duty Products, Switched
Twist-Lock®, Industrial Grade,
Accessories, Mechanical Interlock,
30A 600V AC, Single Conductor,
Terminal Screws, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBLMITL](#)



Heavy Duty Products, Switched Twist-Lock®, Industrial Grade,
Accessories, Mechanical Interlock, 30A 600V AC, Single
Conductor, Terminal Screws, Gray

Features

- Unfused Mechanical Interlock for Watertight Safety-Shroud
- Virtually Eliminates Possible Circuit Making or Breaking While Under Load
- Compact, Corrosion Resistant Type 4X Non-metallic Enclosure
- Molded Valox Resists Abuse, Corrosion and Enhances Safety

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage
- Electrical - Dielectric Voltage - Withstands 3,000V minimum
- Electrical - Max. Working Voltage - 600V RMS
- Electrical - Operations - Mechanical 10,000 cycles
- Electrical 6,000 cycles
- Environmental - Flammability - Meets UL 94V0 material classification
- Environmental - Moisture Resistance - IP66 suitability
- Environmental - Operating Temperature - Maximum continuous +75°C Minimum continuous -40°C
- Environmental - UV Resistance - All exposed materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - External full adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of the external label and receptacle face
- Mechanical - Terminal Identification - In accordance with UL, CSA

General

Catalog Number	HBLMITL
Color	Gray
EU RoHS Indicator	No
Item Type	Safety-Shroud Enclosure
Specifications	• Base - PBT • Conduit Hub - Zinc ¾" watertight

Style
Type
UPC

- Enclosure Gasket - Neoprene
 - Handle - PBT
 - Shaft - PBT
 - Top - PBT
- For 20A and 30A Devices
Switched Enclosure
783585176802

Dimensions

Dimensions	11.44 in x 4.88 in x 4.19 in
Height	4.19 in
Length	11.44 in
Weight	3.65 lb
Width	4.88 in

Electrical Ratings

Dielectric Strength	Withstands 3,000V minimum
---------------------	---------------------------

Certifications And Compliance

Industry Standard(s)	• CSA Certified TYPE 4, 4X and TYPE 12K Enclosure Rating • Listed to UL Standard Type 4X
Nema Rating	Type 4X

Logistics

Carton Quantity	1
Pallet Quantity	290

Product Assets

[Brochures - Circuit-Lock® Motor Disconnects](#)
[Catalog Page - WDK B-34](#) [Catalog Page](#)
[Catalog Page - WDK C-3](#) [Catalog Page](#)
[Catalog Page - WDK B-41](#) [Catalog Page](#)
[Catalog Page - WDK B-22](#) [Catalog Page](#)
[Catalog Page - WDK B-20](#) [Catalog Page](#)

[Catalog Page - WDK B-30 Catalog Page](#)
[Catalog Page - WDK B-32 Catalog Page](#)
[Catalog Page - WDK B-26 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBLMITL AutoCAD Drawing](#)
[Installation Manuals - WIRING_HBLMITL_INSTALLINST](#)
[Literature - Circuit-Lock® Motor Disconnects](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)

[Literature - Industrial Solutions](#)
[Literature - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)
[Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
[Sales Drawings - WDK_HBLMITL_DRAWING_PDF](#)
[Specifications - Wiring HBLMITL Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-HBLMITL-SPEC-EN | REV 7/2025