

Heavy Duty Products, IEC Pin and Sleeve Devices, Switched, IEC 309, Male Plug, 30A 250V, 2-Pole 3-Wire Grounding, NEMA 4X/IP67, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL330P6W](#)



Heavy Duty IEC Pin and Sleeve Switched, IEC 309 Male Plug, 30A 250V, 2-Pole 3-Wire Grounding, NEMA 4X/IP67, Watertight

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBL330P6W
Color	Blue
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585550787

Electrical Ratings

Amperage Rating	30/32 A
Current / Amperage Rating	30/32 A
Voltage Rating	250 VAC/220-240 VAC
Voltage Rating Description	250 VAC/220-240 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL330P6W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1303_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Sales Drawings - WDK_HBL330_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-HBLS330P6W-SPEC-EN | REV 6/2024