

Heavy Duty Products, IEC Pin and Sleeve Devices, Switched, IEC 309, Male Plug, 30A 480V, 2-Pole 3-Wire Grounding, NEMA 4X/IP67, Watertight

By Hubbell Wiring Device-Kellems

Catalog # [HBLS330P7W](#)

Heavy Duty IEC Pin and Sleeve Switched, IEC 309 Male Plug, 30A 480V, 2-Pole 3-Wire Grounding, NEMA 4X/IP67, Watertight

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBLS330P7W
Color	Red
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585550794

Electrical Ratings



Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

Catalogs - WDK Catalog Full 2024
Engineering Drawing - HBLS330P7W AutoCAD Drawing
Installation Manuals - WIRING_PD1303_INSTALLINST
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Sales Drawings - WDK_HBLS330_DRAWING_PDF
Specifications - HBLS330P7W
Warranty - Industrial & Commercial Products
Video - Advantage Series Switch-Rated Pin & Sleeve