

Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60A 125V, 2-Pole 3-Wire, NEMA 4X/IP 69K,

By Hubbell Wiring Device-Kellems

Catalog # [HBL360P4W](#)



Heavy Duty IEC Pin and Sleeve, Plug, Switched, 60A 125V, 2-Pole 3-Wire, NEMA 4X/IP 69K,

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBL360P4W
Color	Yellow
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585478982

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Engineering Drawing - HBL360P4W AutoCAD Drawing](#)

[Installation Manuals - WIRING_PD1303_INSTALLINST](#)

[Literature - Pulp & Paper Solutions](#)

[Literature - PULP & PAPER SOLUTIONS](#)

[Sales Drawings - WDK_HBL360P4W_DRAWINGS_PDF](#)

[Warranty - Industrial & Commercial Products](#)

[Video - Advantage Series Switch-Rated Pin & Sleeve](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-HBLS360P4W-SPEC-EN | REV 6/2024