

Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60A 250V/63A 220-240, 2-Pole 3-Wire, NEMA 4X/IP 69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL360P6W](#)



Heavy Duty IEC Pin and Sleeve, Plug, Switched, 60A 250V/63A 220-240,2-Pole 3-Wire, NEMA 4X/IP 69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBL360P6W
Color	Blue
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585478999

Electrical Ratings

Amperage Rating	60/63 A
Current / Amperage Rating	60/63 A
Voltage Rating	250 VAC/220-250 VAC
Voltage Rating Description	250 VAC/220-250 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL360P6W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1303_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Safety Product Guide](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Sales Drawings - WDK_HBL360P6W_DRAWINGS_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-HBLS360P6W-SPEC-EN | REV 6/2024