

Heavy Duty Products, IEC Pin and Sleeve, Receptacle, Switched, 60A 480V AC, 2-Pole 3-Wire Grounding, NEMA4X/IP69K

By Hubbell Wiring Device-Kellems  
Catalog # [HBL360R7W](#)

Heavy Duty IEC Pin and Sleeve, Receptacle, Switched, 60A 480V AC, 2-Pole 3-Wire Grounding, NEMA4X/IP69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBL360R7W
Color	Red
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Receptacle
UPC	783585478555

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A



Voltage Rating	480 VAC
Voltage Rating Description	480 VAC

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

- [Catalog Page - WDK G-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL360R7W AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2660\\_INSTALLINST](#)
- [Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_HBL360R\\_DRAWING\\_PDF](#)
- [Specifications - Wiring HBL360R7W Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)