

Heavy Duty Products, Pin and Sleeve Devices, Switched, IEC 309, Female Connector, 30A 3-Phase 250V, 3-Pole 4-Wire Grounding, NEMA 4X/IP67, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBLS430C9W](#)

Heavy Duty Products, Pin and Sleeve Devices, Switched, IEC 309, Female Connector, 30A 3-Phase 250V, 3-Pole 4-Wire Grounding, NEMA 4X/IP67, Watertight

General

Catalog Number	HBLS430C9W
Color	Blue
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	3-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Connector
UPC	783585550459

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Number Of Wires	4-Wire
-----------------	--------



Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBLS430C9W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2636_INSTALLINST](#)
- [Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
- [Literature - Safety Product Guide](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_HBLS430C9W_DRAWING_PDF](#)
- [Specifications - Wiring HBLS430C9W Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)