

IEC Pin and Sleeve, Industrial, Plug,  
30A 600V Max, 3-Pole 4-Wire, 3  
Control Contacts, NEMA 4X/IP67,  
Watertight, Black

By Hubbell Wiring Device-Kellems  
Catalog # [HBSL430P5WC](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Switched, IEC 309, Male, Plug, 30A 600V, 3-Pole 4-Wire Grounding, 3 Control Contacts, NEMA 4X/IP67, Watertight, Black

Features

- Solid one-piece pins for reliable electrical contact
- Gasketed sealing ring provides watertight seal
- Heavy duty external cord grips

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC Min
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - HB or Better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperature - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing.
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBSL430P5WC
Color	Black
Ingress Protection	4X/IP69k
Insulation	Insulated Body
Material	Thermoplastic
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact



Type	Watertight Plug
UPC	783585679976

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Dielectric Strength	Withstands 3000V Minimum in
Phase	Three Phase
Voltage Rating Description	600 VAC Max

Conductor Related

Cord Type	All Portable
Number Of Wires	4-Wire
Wire Size	#12 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Standard C22.2 No. 182.1</li><li>• UL Classified to IEC60309-1</li><li>• UL Listed, File E146033</li></ul>
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - IHubbell-PRO EC pin & sleeve devices](#)
- [Sales Drawings - M-13982](#)
- [Specifications - WIRING\\_HBSL430P5WC\\_spec](#)
- [Video - Advantage Series Switch-Rated Pin and Sleeve with Auxiliary Contacts](#)
- [Video - Inside the Advantage™ Series Switch-Rated Pin & Sleeve](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
WDK-HBLS430P5WC-SPEC-EN | REV 4/2025