

Heavy Duty Products, IEC Pin and Sleeve, Inlet, Switched, 60/63A 125/250V, 3-Pole 4-Wire Grounding, NEMA 4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL5460B9W](#)



Heavy Duty IEC Pin and Sleeve, Inlet, Switched, 60/63A 125/250V, 3-Pole 4-Wire Grounding, NEMA 4X/IP69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

| | |
|-----------------|------------------------|
| Catalog Number | HBL5460B9W |
| Color | Blue |
| Number Of Poles | 3-Pole |
| Series | Advantage Switch-Rated |
| Style | IP69k NEMA 4X |
| Type | Watertight Inlet |
| UPC | 783585479293 |

Electrical Ratings

| | |
|----------------------------|-----------------|
| Amperage Rating | 60/63 A |
| Current / Amperage Rating | 60/63 A |
| Voltage Rating | 3 Phase 250 VAC |
| Voltage Rating Description | 3 Phase 250 VAC |

Conductor Related

| | |
|-----------------|--------|
| Number Of Wires | 4-Wire |
|-----------------|--------|

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL5460B9W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1304_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_HBL5460B_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Advantage Series Switch-Rated Pin & Sleeve](#)



A Hubbell brand