

Heavy Duty Products, IEC Pin and Sleeve, Connector, Switched, 60A 125/250V AC, 3-Pole 4-Wire Grounding, NEMA4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBLS460C12W](#)

Heavy Duty IEC Pin and Sleeve, Connector, Switched, 60A 125/250V AC, 3-Pole 4-Wire Grounding, NEMA4X/IP69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBLS460C12W
Color	Orange
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	3-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Connector
UPC	783585478562

Electrical Ratings

Amperage Rating	60 A
Current / Amperage Rating	60 A
Voltage Rating	125/250 VAC



Voltage Rating Description	125/250 VAC
----------------------------	-------------

Conductor Related

Number Of Wires	4-Wire
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBLS460C12W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2636_INSTALLINST](#)
- [Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - Food Processing Guide](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Sales Drawings - WDK_HBLS460C_DRAWING_PDF](#)
- [Specifications - Wiring HBLS460C12W Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)