

Heavy Duty Products, IEC Pin and Sleeve, Connector, Switched, 60/63A 3-Phase 380-415V AC, 3-Pole 4-Wire Grounding, NEMA 4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBLS460C6W](#)

Heavy Duty IEC Pin and Sleeve, Connector, Switched, 60/63A 3-Phase 380-415V AC, 3-Pole 4-Wire Grounding, NEMA 4X/IP69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

| | |
|-------------------|------------------------|
| Catalog Number | HBLS460C6W |
| Color | Red |
| EU RoHS Indicator | Contact Manufacturer |
| Number Of Poles | 3-Pole |
| Series | Advantage Switch-Rated |
| Style | IP69k NEMA 4X |
| Type | Watertight Connector |
| UPC | 783585478586 |

Electrical Ratings

| | |
|---------------------------|---------|
| Amperage Rating | 60/63 A |
| Current / Amperage Rating | 60/63 A |



| | |
|----------------------------|-------------|
| Voltage Rating | 380-415 VAC |
| Voltage Rating Description | 380-415 VAC |

Conductor Related

| | |
|-----------------|--------|
| Number Of Wires | 4-Wire |
|-----------------|--------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog Page - WDK G-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBLS460C6W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2636_INSTALLINST](#)
- [Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_HBLS460C_DRAWING_PDF](#)
- [Specifications - Wiring HBLS460C6W Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)