

# Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60A 125/250V, 3-Pole 4-Wire, NEMA 4X/IP 69K

By Hubbell Wiring Device-Kellems  
Catalog # [HBLS460P12W](#)

Heavy Duty IEC Pin and Sleeve, Plug, Switched, 60A 125/250V, 3-Pole 4-Wire, NEMA 4X/IP 69K

## Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

## General

Catalog Number	HBLS460P12W
Color	Orange
Number Of Poles	3-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585479019

## Electrical Ratings



Amperage Rating	60 A
Current / Amperage Rating	60 A
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

## Conductor Related

Number Of Wires	4-Wire
-----------------	--------

## Product Assets

<a href="#">Catalogs - WDK Catalog Full 2024</a>
<a href="#">Engineering Drawing - HBLS460P12W AutoCAD Drawing</a>
<a href="#">Installation Manuals - WIRING_PD1303_INSTALLINST</a>
<a href="#">Literature - PULP &amp; PAPER SOLUTIONS</a>
<a href="#">Literature - Pulp &amp; Paper Solutions</a>
<a href="#">Literature - Food Processing Guide</a>
<a href="#">Sales Drawings - WDK_HBLS460P_DRAWINGS_PDF</a>
<a href="#">Specifications - HBLS460P12W</a>
<a href="#">Warranty - Industrial &amp; Commercial Products</a>
<a href="#">Video - Advantage Series Switch-Rated Pin &amp; Sleeve</a>