

# Heavy Duty Products, Pin and Sleeve Devices, Switched, IEC 309, Male Plug, 30A 120/208V, 4-Pole 5-Wire Grounding, NEMA 4X/IP67, Watertight



By Hubbell Wiring Device-Kellems  
Catalog # [HBL530P9W](#)

Heavy Duty Pin and Sleeve Devices, Switched, IEC 309 Male Plug, 30A 120/208V, 4-Pole 5-Wire Grounding, NEMA 4X/IP67, Watertight

## Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

## General

Catalog Number	HBL530P9W
Color	Blue
Number Of Poles	4-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585550947

## Electrical Ratings

Amperage Rating	30/32 A
-----------------	---------

Current / Amperage Rating	30/32 A
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC

## Conductor Related

Number Of Wires	5-Wire
-----------------	--------

## Logistics

Carton Quantity	10 EA
-----------------	-------

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBL530P9W AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1303\\_INSTALLINST](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Literature - Safety Product Guide](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_HBL530P\\_DRAWING\\_PDF](#)  
[Specifications - HBL530P9W](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Advantage Series Switch-Rated Pin & Sleeve](#)