

Heavy Duty Products, Pin and Sleeve Devices, Switched, IEC 309, Receptacle, 30A 200/346-240/415V, 4-Pole 5- Wire Grounding, NEMA 4X/IP67, Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [HBL530R6W](#)

Heavy Duty Pin and Sleeve Devices, Switched, IEC 309, Receptacle, 30A 200/346-240/415V, 4-Pole 5-Wire Grounding, NEMA 4X/IP67, Watertight

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBL530R6W
Color	Red
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	4-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Receptacle
UPC	783585550596

Electrical Ratings

Amperage Rating	30/32 A
Current / Amperage Rating	30/32 A
Voltage Rating	<ul style="list-style-type: none"><li>• 200/346-240/415 V</li></ul>



Voltage Rating Description	<ul style="list-style-type: none"><li>• 220/380-240/415 V</li></ul> 200/346-240/415 V;220/380-240/415 V
----------------------------	---

Conductor Related

Number Of Wires	5-Wire
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-6 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL530R6W AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2660\\_INSTALLINST](#)
- [Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_HBL530\\_DRAWING\\_PDF](#)
- [Specifications - Wiring HBL530R6W Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)