

Heavy Duty Products, IEC Pin and Sleeve, Plug, Switched, 60A 277/480V AC, NEMA 4X/IP69K

By Hubbell Wiring Device-Kellems
Catalog # [HBL560P7W](#)

Heavy Duty IEC Pin and Sleeve, Plug, Switched, 60A 277/480V AC, NEMA 4X/IP69K

Features

- Mates with existing installed base of IEC 60309-2 pin and sleeve devices
- Approved as a disconnecting means for motor circuits and branch circuits
- UL Type 4X, 12 and IP69k environmental ratings
- Impact and corrosion-resistant PBT that is color coded by voltage
- Unswitched ground and power indicating LED lights

General

Catalog Number	HBL560P7W
Color	Red
Number Of Poles	4-Pole
Series	Advantage Switch-Rated
Style	IP69k NEMA 4X
Type	Watertight Plug
UPC	783585479088

Electrical Ratings



Amperage Rating	60 A
Current / Amperage Rating	60 A
Voltage Rating	3 Phase Y 277/480 VAC
Voltage Rating Description	3 Phase Y 277/480 VAC

Conductor Related

Number Of Wires	5-Wire
-----------------	--------

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL560P7W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1303_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Safety Product Guide](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_HBL560P7W_DRAWING_PDF](#)
- [Specifications - HBL560P7W](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Advantage Series Switch-Rated Pin & Sleeve](#)