



Wiring Device-Kellems

Patch Cord, Speed Gain, Cat5E, Slim, Black, 10'

By Hubbell Wiring Device-Kellems
Catalog # [HC5EBK10](#)



Patch Cord, Speed Gain, Cat5E, Slim, Black, 10'

General

Attenuation	.1dB
Boot Type	PVC
Color	Black
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none"> Mechanical - Cable to plug tensile strength - 20+ lbs. Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620234281

Dimensions

Length	10 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> ANSI/TIA/EIA-568-C.2 Category 5E Component ISO 11801/60603-7-41 Category 5E Component
----------------------	--------------------------------------------------------------------------------------------------------------------------------------------------

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [HC5EBK25 - Patch Cord, Speed Gain, Cat5E, Slim, Black, 25'](#)
- [HC5EOR10 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 10' Length, Orange](#)
- [HC5EGY10 - Patch Cord, Speed Gain, Cat5E, Slim, Gray, 10'](#)
- [HC5EBK01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Black](#)
- [HC5EBK20 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 20' Length, Black](#)



A proud member of the Hubbell Family.