



# Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Green

By Hubbell Wiring Device-Kellems  
Catalog # [HC5EGN01](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Green

## Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

## General

Attenuation	.1dB
Boot Type	PVC
Color	Green
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620234700

## Dimensions

Length	1 ft
Outside Diameter	0.218

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

## Product Assets

[Warranty - Industrial & Commercial Products](#)

## Related Products

- [HC5ER01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Red](#)
- [HC5EP01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Purple](#)
- [HC5EBK01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Black](#)
- [HC5EGN10 - Patch Cord, Speed Gain, Cat5E, Slim, Green, 10'](#)
- [HC5EW01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HC5EGN01-SPEC-EN | REV 5/2023