



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Green

By Hubbell Wiring Device-Kellems
Catalog # [HC5EGN25](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Green

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Color	Green
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none">• Mechanical - Cable to plug tensile strength - 20+ lbs.• Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620234779

Dimensions

Length	25 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating 300V AC kV

Conductor Related

Conductor Stranding Stranded
Conductor Type Copper
Number Of Conductors 8-Conductor
Wire Size #24 AWG

Certifications and Compliance

Industry Standard(s)

- ANSI/TIA/EIA-568-C.2 Category 5E Component
- ISO 11801/60603-7-41 Category 5E Component

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

[HC5EGN07 - Patch Cord, Speed Gain, Cat5E, Slim, Green, 7'](#)
[HC5EGN10 - Patch Cord, Speed Gain, Cat5E, Slim, Green, 10'](#)
[HC5ER25 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Red](#)
[HC5EOR25 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Orange](#)
[HC5EPK25 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Pink](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HC5EGN25-SPEC-EN | REV 5/2023