



Wiring Device-Kellems

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Orange



By Hubbell Wiring Device-Kellems
Catalog # [HC5EOR01](#)

Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Orange

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Color	Orange
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620235165

Dimensions

Length	1 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating 300V AC kV

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [HC5EPK01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Pink](#)
- [HC5ER01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Red](#)
- [HC5EOR03 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 3' Length, Orange](#)
- [HC5EOR15 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 15' Length, Orange](#)
- [HC5EBK01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Black](#)



A proud member of the Hubbell Family.