



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 3' Length, Pink

By Hubbell Wiring Device-Kellems
Catalog # [HC5EPK03](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 3' Length, Pink

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

Application

Category 5e

General

Attenuation	.1dB
Boot Type	PVC
Color	Pink
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
UPC	662620235639

Dimensions

Outside Diameter	0.218
------------------	-------

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [HC5EBK03 - Patch Cord, Speed Gain, Cat5E, Slim, Black, 3'](#)
- [HC5EPK25 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Pink](#)
- [HC5EPK15 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 15' Length, Pink](#)
- [HC5EPK05 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 5' Length, Pink](#)
- [HC5EGY03 - Patch Cord, Speed Gain, Cat5E, Slim, Gray, 10'](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HC5EPK03-SPEC-EN | REV 5/2023