



Patch Cord, Speed Gain, Cat5E, Slim, White, 3' Length

By Hubbell Wiring Device-Kellems
Catalog # [HC5EW03](#)



Patch Cord, Speed Gain, Cat5E, Slim, White, 3' Length

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Color	White
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none">• Mechanical - Cable to plug tensile strength - 20+ lbs.• Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620236490

Dimensions

Length	3 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 5E Component• ISO 11801/60603-7-41 Category 5E Component
----------------------	---------------------------------------------------------------------------------------------------------------------------------------------------

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

[HC5EPK03 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 3' Length, Pink](#)
[HC5EW10 - Patch Cord, Speed Gain, Cat5E, Slim, White, 10'](#)
[HC5EY03 - Patch Cord, Speed Gain, Cat5E, Slim, Yellow, 3'](#)
[HC5EW07 - Patch Cord, Speed Gain, Cat5E, Slim, White, 7'](#)
[HC5EW15 - Patch Cord, Speed Gain, Cat5E, Slim, White, 15'](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HC5EW03-SPEC-EN | REV 5/2023