



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HC5EY01](#)



Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Yellow

Features

- Verified Category 5E Component Exceeds TIA Limits
- Plug Optimized For High Density Switch Ports
- Gigabit Assurance
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Color	Yellow
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620236711

Dimensions

Length	1 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	Meets And Exceeds ANSI/TIA
----------------------	----------------------------

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [HC5EY03 - Patch Cord, Speed Gain, Cat5E, Slim, Yellow, 3'](#)
- [HC5EY25 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Yellow](#)
- [HC5EGN01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Green](#)
- [HC5EB01 - Patch Cord, Speed Gain, Cat5E, Slim, Blue, 1'](#)
- [HC5ER01 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 1' Length, Red](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HC5EY01-SPEC-EN | REV 5/2023