



Patch Cord, Speed Gain, Cat5E, Slim, Yellow, 7'

By Hubbell Wiring Device-Kellems
Catalog # [HC5EY07](#)



Patch Cord, Speed Gain, Cat5E, Slim, Yellow, 7'

General

Attenuation	.1dB
Boot Type	PVC
Color	Yellow
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none">Mechanical - Cable to plug tensile strength - 20+ lbs.Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620236742

Dimensions

Length	7 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">ANSI/TIA/EIA-568-C.2 Category 5E ComponentISO 11801/60603-7-41 Category 5E Component
----------------------	---

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [HC5EB07 - Patch Cord, Speed Gain, Cat5E, Slim, Blue, 7'](#)
- [HC5EW07 - Patch Cord, Speed Gain, Cat5E, Slim, White, 7'](#)
- [HC5EGY07 - Patch Cord, Speed Gain, Cat5E, Slim, Gray, 10'](#)
- [HC5EOR07 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 7' Length, Orange](#)
- [HC5EY25 - Copper Solutions, Patch Cords, SPEEDGAIN, Cat 5e, Slim, 25' Length, Yellow](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HC5EY07-SPEC-EN | REV 5/2023