



Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 25' Length, Orange

By Hubbell Wiring Device-Kellems
Catalog # [HC6OR25](#)



Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 25' Length, Orange

General

Attenuation	.1dB
Boot Type	PVC
Color	Orange
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none">Mechanical - Cable to plug tensile strength - 20+ lbs.Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620232706

Dimensions

Length	25 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">ANSI/TIA/EIA-568-C.2 Category 6 ComponentISO 11801/60603-7-41 Category 6 Component
----------------------	---

Logistics

Carton Quantity	12
-----------------	----

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [HC6B25 - Patch Cord, Speed Gain, Cat6, Slim, Blue, 25'](#)
- [HC6OR10 - Patch Cord, NextSpeed, Cat6, Slim, Orange, 10' Length](#)
- [HC6OR15 - Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 15' Length, Orange](#)
- [HC6OR07 - Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 7' Length, Orange](#)
- [HC6OR05 - Patch Cord, Speed Gain, Cat6, Slim, Orange, 5'](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HC6OR25-SPEC-EN | REV 5/2023