



Wiring Device-Kellems

# Patch Cord, Speed Gain, Cat6, Slim, Purple, 10'

By Hubbell Wiring Device-Kellems  
Catalog # [HC6P10](#)



Patch Cord, Speed Gain, Cat6, Slim, Purple, 10'

## General

Attenuation	.1dB
Boot Type	PVC
Color	Purple
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none"> <li>Mechanical - Cable to plug tensile strength - 20+ lbs.</li> <li>Mechanical - Mating Cycles - 2000+</li> </ul>
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620232904

## Dimensions

Length	10 ft
Outside Diameter	0.218

## Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

## Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>ANSI/TIA/EIA-568-C.2 Category 6 Component</li> <li>ISO 11801/60603-7-41 Category 6 Component</li> </ul>
----------------------	--

## Product Assets

[Warranty - Industrial & Commercial Products](#)

## Related Products

- [HC6P20 - Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 20' Length, Purple](#)
- [HC6B10 - Patch Cord, Speed Gain, Cat6, Slim, Blue, 10'](#)
- [HC6P25 - Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 25' Length, Purple](#)
- [HC6BK10 - Patch Cord, Speed Gain, Cat6, Slim, Black, 10'](#)
- [HC6GY10 - Patch Cord, Speed Gain, Cat6, Slim, Gray, 10'](#)



A proud member of the Hubbell Family.