

## Patch Cord, Speed Gain, Cat6, Slim, Red, 7'

By Hubbell Wiring Device-Kellems  
Catalog # [HC6R07](#)



Patch Cord, Speed Gain, Cat 6,Slim, 7'

### Performance

- Mechanical - Cable to plug tensile strength - 20+ lbs.
- Mechanical - Mating Cycles - 2000+

### General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6R07
Color	<ul style="list-style-type: none"><li>• Red</li><li>•</li></ul>
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	RJ45
Temperature Rating	Per TIA
Type	<ul style="list-style-type: none"><li>• Standard</li><li>• Standard</li></ul>
UPC	662620233352

### Dimensions

Length	7 ft
Outside Diameter	0.218

### Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

### Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• ANSI/TIA/EIA-568-C.2 Category 6 Component</li><li>• ISO 11801/60603-7-41 Category 6 Component</li></ul>
----------------------	---

### Product Assets

[Catalog Page - PREM D5 CatalogPage](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Warranty - Industrial & Commercial Products](#)