



Patch Cord, Speed Gain, Cat6, Slim, White, 3'

By Hubbell Wiring Device-Kellems
Catalog # [HC6W03](#)



Patch Cord, Speed Gain, Cat6, Slim, White, 3'

Features

- Third Party Verified Category 6 Component
- Plug Optimized For High Density Switch Ports
- TSB-155 10 Gig Support
- Qualified to 150% of 802.3bt PoE Current Level

General

Attenuation	.1dB
Boot Type	PVC
Color	<ul style="list-style-type: none">• White• Blanc
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none">• Mechanical - Cable to plug tensile strength - 20+ lbs.• Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620233567

Dimensions

Length	3 ft
Outside Diameter	0.218

Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• ANSI/TIA/EIA-568-C.2 Category 6 Component• ISO 11801/60603-7-41 Category 6 Component
----------------------	---

Logistics

Carton Quantity	65
-----------------	----

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

[HC6B03 - Patch Cord, Speed Gain, Cat6, Slim, Blue, 3'](#)
[HC6W10 - Patch Cord, Speed Gain, Cat6, Slim, White, 10'](#)
[HC6GY03 - Patch Cord, Speed Gain, Cat6, Slim, Gray, 3'](#)
[HC6W07 - Patch Cord, Speed Gain, Cat6, Slim, White, 7'](#)
[HC6W15 - Patch Cord, Speed Gain, Cat6, Slim, White, 15'](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HC6W03-SPEC-EN | REV 5/2023