

## Patch Cord, Speed Gain, Cat6, Slim, Yellow, 7'

By Hubbell Wiring Device-Kellems  
Catalog # [HC6Y07](#)



Patch Cord, Speed Gain, Cat 6,Slim, 7'

### General

Attenuation	.1dB
Boot Type	PVC
Catalog Number	HC6Y07
Color	Yellow
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	Mechanical - Cable to plug tensile strength - 20+ lbs. Mechanical - Mating Cycles - 2000+
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
	Standard
UPC	662620233819

### Dimensions

Length	7 ft
Outside Diameter	0.218

### Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

### Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number of Conductors	8-Conductor
Wire Size	#24 AWG

### Certifications And Compliance

Industry Standard(s)	ANSI/TIA/EIA-568-C.2 Category 6 Component ISO 11801/60603-7-41 Category 6 Component
----------------------	---

### Logistics

Carton Quantity	50
Pallet Quantity	2700

### Product Assets

[Catalog Page - PREM D5 CatalogPage](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Catalogs - Premise Wiring Catalog](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-HC6Y07-SPEC-EN | REV 6/2024