



## Patch Cord, Speed Gain, Cat6, Slim, Yellow, 15'

By Hubbell Wiring Device-Kellems  
Catalog # [HC6Y15](#)



Patch Cord, Speed Gain, Cat6, Slim, Yellow, 15'

### General

Attenuation	.1dB
Boot Type	PVC
Color	Yellow
EU RoHS Indicator	Yes
Item Type	NEXTSPEED Category 6 and 5e Patch Cords
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Performance	<ul style="list-style-type: none"><li>Mechanical - Cable to plug tensile strength - 20+ lbs.</li><li>Mechanical - Mating Cycles - 2000+</li></ul>
Plug Type	RJ45
Temperature Rating	Per TIA
Type	Standard
UPC	662620233833

### Dimensions

Length	15 ft
Outside Diameter	0.218

### Electrical Ratings

Voltage Rating	300V AC kV
----------------	------------

### Conductor Related

Conductor Stranding	Stranded
Conductor Type	Copper
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

### Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>ANSI/TIA/EIA-568-C.2 Category 6 Component</li><li>ISO 11801/60603-7-41 Category 6 Component</li></ul>
----------------------	---------------------------------------------------------------------------------------------------------------------------------------------

### Product Assets

[Warranty - Industrial & Commercial Products](#)

### Related Products

- [HC6BK15 - Patch Cord, Speed Gain, Cat6, Slim, Black, 15'](#)
- [HC6P15 - Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 15' Length, Purple](#)
- [HC6Y01 - Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 1' Length, Yellow](#)
- [HC6OR15 - Copper Solutions, Patch Cords, NEXTSPEED, Cat 6, Slim, 15' Length, Orange](#)
- [HC6GN15 - Patch Cord, Speed Gain, Cat6, Slim, Green, 15'](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HC6Y15-SPEC-EN | REV 5/2023