

# Signal And Control Products, Field Attachable Mini-Quick Male Plug, Right Angled, 4-Pole

By Hubbell Wiring Device-Kellems

Catalog # [HCMS04F13](#)



Signal And Control Products, Field Attachable Mini-Quick Male Plug, Right Angled, 4-Pole

## Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

## General

Application	Quick Connect/Disconnect Signal and Control
EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Female Straight Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Deg C to 85 Deg C
Performance	Electrical - Amperage - 3 Pin - 12A  4,5 Pin - 9A  Electrical - Maximum Wire Size - #16 AWG  Electrical - Voltage Rating - 250V  Environmental - Moisture Resistance - IP66 Suitability  Environmental - Operating Temperature - -40°C to 85°C
Thread Size	Non-Threaded
UPC	783585192109

## Electrical Ratings

Amperage Rating	9 A
Current / Amperage Rating	9 A
Current Rating	9 A
Voltage Rating	250V kV

## Conductor Related

Cable Size	.39"-.47"
Cable Specification	UL Listed Portable Cord

## Certifications And Compliance

Industry Standard(s)	CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07  UL 2238 and UL50E, File No. E192071
----------------------	---

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Pulp & Paper Solutions](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Sales Drawings - WDK\\_HCMS04F13\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK-HCMS04F13-SPEC-EN | REV 6/2024