



Signal and Control Products, Mini-Quick, Female Plug, 5-Pole, Field Attachable, F16

By Hubbell Wiring Device-Kellems
Catalog # [HCMS05F16](#)



Signal and Control Products, Mini-Quick, Female Plug, 5-Pole, Field Attachable, F16

Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

Application

Quick Connect/Disconnect Signal and Control

General

EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Female Straight Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Deg C to 85 Deg C
Performance	<ul style="list-style-type: none">• Electrical - Amperage - 3 Pin - 12A• 4,5 Pin - 9A• Electrical - Maximum Wire Size - #16 AWG• Electrical - Voltage Rating - 250V• Environmental - Moisture Resistance - IP66 Suitability• Environmental - Operating Temperature - -40°C to 85°C
Thread Size	Non-Threaded
UPC	783585192239

Electrical Ratings

Amperage Rating	9 A
Current / Amperage Rating	9 A
Current Rating	9 A
Voltage Rating	250V kV

Conductor Related

Cable Size	.47"-.55"
Cable Specification	UL Listed Portable Cord

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071
----------------------	--

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HCMS05F16_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-HCMS05F16-SPEC-EN | REV 5/2023

