

# CableTrak Kits less Brackets, 1', 101 Series

By Hubbell Wiring Device-Kellems  
Catalog # [HCT101141](#)

CableTrak Kits less Brackets, 1', 101 Series



## General

Application	Cable and Hose Carrier
Catalog Number	HCT101141
Color	Black
EU RoHS Indicator	No
Item Type	CableTrak Extender Kit
Material	Nylon, Fiberglass Reinforced
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Environmental - Max. Operating Speed - 600 FPM (feet per minute), 180 MPM (meters per minute).  Environmental - Max. Unsupported Travel Distance - HCT16 Series without sag 9 ft. (2.8 m) with sag 10.5 ft. (3.2 m) HCT25 Series without sag 13.5 ft. (4.1 m) with sag 17 ft. (5.2 m)  Environmental - Operating Temperature - Continuous +20°F to +100°F (-7°C to 38°C) Intermittent* -40°F to +220°F (-40°C to 104°C).
UPC	783585343303

## Dimensions

Depth	0.75
Display Size	Standard Sized
Width	0.59 in

## Electrical Ratings

Connectivity	Snap Together Sections
--------------	------------------------

## Conductor Related

Wire Size	.531"
-----------	-------

## Logistics

Carton Quantity	6
-----------------	---

## Product Assets

- [Brochures - POWERTRAK® GRP Non-Metallic Cable/Hose Carrier](#)
- [Catalog Page - WDK I-10 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING\\_PD1465\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_HCT101141\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK-HCT101141-SPEC-EN | REV 6/2024