

CableTrak Kits with Brackets, 4', 163 Series

By Hubbell Wiring Device-Kellems
Catalog # [HCT16434K](#)

CableTrak Kits with Brackets, 4', 163 Series

Features

- Flip top link design
- Fiberglass reinforced nylon construction
- Highly wear resistant design provides corrosion resistance

Application

- Cable and Hose Carrier

Performance

- Environmental - Max. Operating Speed - 600 FPM (feet per minute), 180 MPM (meters per minute).
- Environmental - Max. Unsupported Travel Distance - HCT16 Series without sag 9 ft. (2.8 m) with sag 10.5 ft. (3.2 m)
- HCT25 Series without sag 13.5 ft. (4.1 m) with sag 17 ft. (5.2 m)
- Environmental - Operating Temperature - Continuous +20°F to +100°F (-7°C to 38°C)
- Intermittent* -40°F to +220°F (-40°C to 104°C).

General

Catalog Number	HCT16434K
Color	Black
EU RoHS Indicator	No
Item Type	CableTrak Extender Kit
Material	Nylon, Fiberglass Reinforced
OEM Brand Name	Hubbell Wiring Device-Kellems



Specifications

UPC

- Applications - Machine tool, robotic automation, material handling
 - Material - Fiberglass reinforced nylon
- 783585343709

Dimensions

Display Size	Standard Sized
Width	4.06 in

Electrical Ratings

Connectivity	Snap Together Sections
--------------	------------------------

Conductor Related

Wire Size	3.654"
-----------	--------

Product Assets

- [Brochures - POWERTRAK® GRP Non-Metallic Cable/Hose Carrier](#)
- [Catalog Page - WDK I-10 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HCT16434K AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1465_INSTALLINST](#)
- [Sales Drawings - WDK_HCT16434K_DRAWINGS_PDF](#)
- [Specifications - HCT16434K](#)
- [Warranty - Industrial & Commercial Products](#)