

Signal And Control Products, Field
Attachable Mini-Quick Male Plug,
Right Angled, 4-Pole

By Hubbell Wiring Device-Kellems
Catalog # [HIMA04F9](#)

Signal And Control Products, Field Attachable Mini-Quick Male
Plug, Right Angled, 4-Pole

Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

Application

Quick Connect/Disconnect Signal and Control

Performance

- Electrical - Amperage - 3 Pin - 12A
- 4,5 Pin - 9A
- Electrical - Maximum Wire Size - #16 AWG
- Electrical - Voltage Rating - 250V
- Environmental - Moisture Resistance - IP66 Suitability
- Environmental - Operating Temperature - -40°C to 85°C

General

Catalog Number	HIMA04F9
EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Male In-Line Angle Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Deg C to 85 Deg C
Specifications	<ul style="list-style-type: none">• Connector Insert - PUR/PA• Connector Shell - PBT• Contacts - Brass, gold plate over palladium nickel



	<ul style="list-style-type: none">• Coupling Nut - Anodized aluminum, SST consult factory
Thread Size	Non-Threaded
UPC	783585192161

Electrical Ratings

Amperage Rating	9 A
Current / Amperage Rating	9 A
Current Rating	9 A
Voltage Rating	250V kV

Conductor Related

Cable Size	.24"- .32"
Cable Specification	UL Listed Portable Cord

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071
----------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_HIMA_DRAWING_PDF](#)
[Specifications - HIMA04F9](#)
[Warranty - Industrial & Commercial Products](#)