



# Signal and Control Products, Mini-Quick, Male Extension Plug, 4-Pole, Field Attachable, F9

By Hubbell Wiring Device-Kellems  
Catalog # [HIMS04F9](#)



Signal and Control Products, Mini-Quick, Male Extension Plug, 4-Pole, Field Attachable, F9

## Features

- Superior Contact Design
- Body with High Impact Design
- Precision Wire Funnels Eliminate Stray Strands

## Application

Quick Connect/Disconnect Signal and Control

## General

EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Male In-Line Straight Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Deg C to 85 Deg C
Performance	<ul style="list-style-type: none"><li>• Electrical - Amperage - 3 Pin - 12A</li><li>• 4,5 Pin - 9A</li><li>• Electrical - Maximum Wire Size - #16 AWG</li><li>• Electrical - Voltage Rating - 250V</li><li>• Environmental - Moisture Resistance - IP66 Suitability</li><li>• Environmental - Operating Temperature - -40°C to 85°C</li></ul>
Thread Size	Non-Threaded
UPC	783585192130

## Electrical Ratings

Amperage Rating	9 A
Current / Amperage Rating	9 A
Current Rating	9 A
Voltage Rating	250V kV

## Conductor Related

Cable Size	.24"- .32"
Cable Specification	UL Listed Portable Cord

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07</li><li>• UL 2238 and UL50E, File No. E192071</li></ul>
----------------------	--

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

[Literature - WIRING\\_WLFVM034](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_HIMS04F9\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-HIMS04F9-SPEC-EN | REV 5/2023

